



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S20700SC00 3/4" SS316 Emt Strut Clamp

Calbrite

Catalog Number	S20700SC00
Manufacturer	Calbrite
Description	Stainless Steel 316 Strut Clamp 3/4" - Emt
Weight per unit	0.1080 (lbs/each)
Product Category	Channel & Strut Fittings

Features

Material	Stainless Steel - 316
Wall Thickness	0.07

Material, Color, and Finish

Color	Polished Silver
Finish	#4 Polished Finish

Dimensions and Weight

Length	2.2
--------	-----

Descriptions

Description	3/4" SS316 EMT STRUT CLAMP
extra long description	CAL S20700SC00 3/4 SS316 EMT STRUT
Features	Stainless strut clamps can be used at any point along the slot side of the channel and are inserted into the two channel returns. Designed for use in standard 1-5/8" channels. Supplied with stainless nut and bolt.
Long Description	Stainless Steel 316 Strut Clamp 3/4" - EMT
Product Type	3/4 SS316 Emt Strut CLMP
Short Description	SS_EMT STR CLMP_316

Manufacturer Information

Brand	CALBRITE
GTIN	00847656011086
Manufacturers Part Number	S20700SC00
UPC	847656011086

Taxonomies, Classifications, and Categories

Type	EMT
------	-----

Trade Size

Trade Size	3/4
------------	-----

Packaging

Carton	1
Weight	0.108
Weight Per foot	0.108