

Specifications

Photo is representative



Eaton S20N11P01P

Eaton General purpose encapsulated transformer, EP, copper, NEMA 3R, 67P, 60 Hz, 180C, 1 kVA, 1 kVA, wall, single-phase, 240 V, 480 V, 120/240 V, NEMA ST-20, NONE, 115 °C rise, 1 KVA, indoor-outdoor, 3A

General specifications

PRODUCT NAME	Eaton General purpose encapsulated transformer
CATALOG NUMBER	S20N11P01P
UPC	786680073687
PRODUCT LENGTH/DEPTH	6.56 in
PRODUCT HEIGHT	13.03 in
PRODUCT WIDTH	5.53 in
PRODUCT WEIGHT	25 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Physical Attributes

COIL MATERIAL	Copper
DESIGN	EP
ENCLOSURE	NEMA 3R
FRAME	67P
INSULATION	180 °C
MOUNTING	Wall
TAP SIZE	None
TYPE	General-Purpose Encapsulated Transformer
WIRING CONNECTION	3A

Performance Ratings

FREQUENCY RATING	60 Hz
KVA RATING	1 kVA
KVA	1 kVA
PHASE	Single-phase
PRIMARY VOLTAGE	240 V, 480 V
SECONDARY VOLTAGE	120/240 V
SOUND LEVEL	NEMA ST-20
TEMPERATURE RISE	115 °C rise
VOLT AMPERE RATING	1 kVA

Miscellaneous

WEATHERSHIELD

Indoor-Outdoor

Resources

CATALOGS

[Commercial Distribution,
Transformers, Volume 2, Tab 2](#)

**SPECIFICATIONS AND
DATASHEETS**

[Eaton Specification Sheet -
S20N11P01P](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights
Reserved.

Eaton is a registered trademark.

All other trademarks are property of
their respective owners.

Follow us on social media to get the latest
product and support information.



Specifications

Photo is representative



Eaton S20N11P01P

Eaton General purpose encapsulated transformer, EP, copper, NEMA 3R, 67P, 60 Hz, 180C, 1 kVA, 1 kVA, wall, single-phase, 240 V, 480 V, 120/240 V, NEMA ST-20, NONE, 115 °C rise, 1 KVA, indoor-outdoor, 3A

General specifications

PRODUCT NAME	Eaton General purpose encapsulated transformer
CATALOG NUMBER	S20N11P01P
UPC	786680073687
PRODUCT LENGTH/DEPTH	6.56 in
PRODUCT HEIGHT	13.03 in
PRODUCT WIDTH	5.53 in
PRODUCT WEIGHT	25 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Physical Attributes

COIL MATERIAL	Copper
DESIGN	EP
ENCLOSURE	NEMA 3R
FRAME	67P
INSULATION	180 °C
MOUNTING	Wall
TAP SIZE	None
TYPE	General-Purpose Encapsulated Transformer
WIRING CONNECTION	3A

Performance Ratings

FREQUENCY RATING	60 Hz
KVA RATING	1 kVA
KVA	1 kVA
PHASE	Single-phase
PRIMARY VOLTAGE	240 V, 480 V
SECONDARY VOLTAGE	120/240 V
SOUND LEVEL	NEMA ST-20
TEMPERATURE RISE	115 °C rise
VOLT AMPERE RATING	1 kVA

Miscellaneous

WEATHERSHIELD

Indoor-Outdoor

Resources

CATALOGS

[Commercial Distribution,
Transformers, Volume 2, Tab 2](#)

**SPECIFICATIONS AND
DATASHEETS**

[Eaton Specification Sheet -
S20N11P01P](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights
Reserved.

Eaton is a registered trademark.

All other trademarks are property of
their respective owners.

Follow us on social media to get the latest
product and support information.

