

# Specifications

## Eaton S20N11P01P

Eaton General purpose encapsulated transformer, EP, copper, NEMA 3R, 67P, 60 Hz, 180C, 1 kVA, 1 kVA, wall, single-phase, 240 V, 480 V, 120/240 V, NEMA ST-20, NONE, 115 °C rise, 1 KVA, indoor-outdoor, 3A



Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton General purpose encapsulated transformer
<b>CATALOG NUMBER</b>	S20N11P01P
<b>UPC</b>	786680073687
<b>PRODUCT LENGTH/DEPTH</b>	6.56 in
<b>PRODUCT HEIGHT</b>	13.03 in
<b>PRODUCT WIDTH</b>	5.53 in
<b>PRODUCT WEIGHT</b>	25 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed



Powering Business Worldwide

## Physical Attributes

<b>COIL MATERIAL</b>	Copper
<b>DESIGN</b>	EP
<b>ENCLOSURE</b>	NEMA 3R
<b>FRAME</b>	67P
<b>INSULATION</b>	180 °C
<b>MOUNTING</b>	Wall
<b>TAP SIZE</b>	None
<b>TYPE</b>	General-Purpose Encapsulated Transformer
<b>WIRING CONNECTION</b>	3A

## Miscellaneous

<b>WEATHERSHIELD</b>	Indoor-Outdoor
----------------------	----------------

## Performance Ratings

<b>FREQUENCY RATING</b>	60 Hz
<b>KVA RATING</b>	1 kVA
<b>KVA</b>	1 kVA
<b>PHASE</b>	Single-phase
<b>PRIMARY VOLTAGE</b>	240 V, 480 V
<b>SECONDARY VOLTAGE</b>	120/240 V
<b>SOUND LEVEL</b>	NEMA ST-20
<b>TEMPERATURE RISE</b>	115 °C rise
<b>VOLT AMPERE RATING</b>	1 kVA

## Resources

<b>CATALOGS</b>	<a href="#">Commercial Distribution, Transformers, Volume 2, Tab 2</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - S20N11P01P</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton S20N11P01P

Eaton General purpose encapsulated transformer, EP, copper, NEMA 3R, 67P, 60 Hz, 180C, 1 kVA, 1 kVA, wall, single-phase, 240 V, 480 V, 120/240 V, NEMA ST-20, NONE, 115 °C rise, 1 KVA, indoor-outdoor, 3A



Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton General purpose encapsulated transformer
<b>CATALOG NUMBER</b>	S20N11P01P
<b>UPC</b>	786680073687
<b>PRODUCT LENGTH/DEPTH</b>	6.56 in
<b>PRODUCT HEIGHT</b>	13.03 in
<b>PRODUCT WIDTH</b>	5.53 in
<b>PRODUCT WEIGHT</b>	25 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed

**EATON**

Powering Business Worldwide

## Physical Attributes

COIL MATERIAL	Copper
DESIGN	EP
ENCLOSURE	NEMA 3R
FRAME	67P
INSULATION	180 °C
MOUNTING	Wall
TAP SIZE	None
TYPE	General-Purpose Encapsulated Transformer
WIRING CONNECTION	3A

## Miscellaneous

WEATHERSHIELD	Indoor-Outdoor
---------------	----------------

## Performance Ratings

FREQUENCY RATING	60 Hz
KVA RATING	1 kVA
KVA	1 kVA
PHASE	Single-phase
PRIMARY VOLTAGE	240 V, 480 V
SECONDARY VOLTAGE	120/240 V
SOUND LEVEL	NEMA ST-20
TEMPERATURE RISE	115 °C rise
VOLT AMPERE RATING	1 kVA

## Resources

CATALOGS	<a href="#">Commercial Distribution, Transformers, Volume 2, Tab 2</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - S20N11P01P</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

