

---

## NON-NEMA 3 WIRE PLUG - BLACK BACK, WHITE FRONT BODY

S2348DF | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Non-Nema Plug, 14amp 125-480V, IP20 Suitability, Black Back, White Front Body



- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6/6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Black, White  
Type: Plug  
Number Of Wires: 3  
Special Features: Non-NEMA

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

UN SPSC: 39121403

#### TECHNICAL INFORMATION

Volts: 125-480V

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant



---

## NON-NEMA 3 WIRE PLUG - BLACK BACK, WHITE FRONT BODY

S2348DF | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Non-Nema Plug, 14amp 125-480V, IP20 Suitability, Black Back, White Front Body



- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6/6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Black, White  
Type: Plug  
Number Of Wires: 3  
Special Features: Non-NEMA

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

UN SPSC: 39121403

#### TECHNICAL INFORMATION

Volts: 125-480V

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

