



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S29405 7W Led PAR20 27K 40 Deg Beam

Satco

Catalog Number	S29405
Manufacturer	Satco
Description	6.5 Watt PAR20 Led Lamp - 2700K - 40 Degree Beam Angle - Medium Base - 120 Volts
Weight per unit	0.2300 (lbs/each)
Product Category	Lighting

Features

average life	25000
Base	Medium
beam angle	40
lumens	520
Material	Plastic
Shape	PAR20
Warranty	3 Year Limited - 12 hr per day

Material, Color, and Finish

color temperature	2700
Finish	Silver

Dimensions and Weight

Size	2.99
------	------

Descriptions

Description	7W LED PAR20 27K 40 DEG BEAM
extra long description	SATCO S29405 6.5PAR20/LED/40'/927/1
Long Description	6.5 Watt PAR20 LED Lamp - 2700K - 40 Degree Beam Angle - Medium Base - 120 Volts
Product Type	6.5PAR20/Led/40'/927/120V
Special Features	Lawful for sale in California ; California T24 Compliant ; Yes - Dimmable ; Lens finish: Clear ; Warranty: 3 Year Limited - 12 hours per day ; Wet location rated ; Material: Plastic ; Incandescent Equivalent: 50W ; Enclosed Fixture Rated: Yes ; Operating Temperature: -20C (-4F) to a maximum of +45C (+113F)

Manufacturer Information

Brand	Satco
GTIN	00045923294051
Manufacturers Part Number	S29405
UPC	045923294051



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LED PAR SHAPE LAMPS

Type LED PAR

Packaging

Carton 1

Weight 0.1

Weight Per each 0.23

Uses, Certifications, and Standards

Operating Temperature -20C (-4F) to a maximum of +45C (+113F)

standard cULus