



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S29431 13W PAR30 Led 30K 40deg

Satco

Catalog Number	S29431
Manufacturer	Satco
Description	12.5 Watt PAR30LN Led Lamp - 3000K - 40 Degree Beam Angle - Medium Base - 120 Volts
Weight per unit	0.3500 (lbs/each)
Product Category	Lighting

Features

average life	25000
Base	Medium
beam angle	40
lumens	1k
Material	Plastic
Shape	PAR30LN
Warranty	3 Year Limited - 12 hr per day

Material, Color, and Finish

color temperature	3000
Finish	Silver

Dimensions and Weight

Size	4.57
------	------

Descriptions

Description	13W PAR30 LED 30K 40DEG
extra long description	SATCO S29431 12.5PAR30/LN/LED/40'/9
Long Description	12.5 Watt PAR30LN LED Lamp - 3000K - 40 Degree Beam Angle - Medium Base - 120 Volts
Product Type	12.5PAR30/LN/Led/40'/930/120V
Special Features	Lawful for sale in California ; California T24 Compliant ; Yes - Dimmable ; Lens finish: Clear ; Warranty: 3 Year Limited - 12 hours per day ; Wet location rated ; Material: Plastic ; Incandescent Equivalent: 75W ; Enclosed Fixture Rated: Yes ; Operating Temperature: -20C (-4F) to a maximum of +45C (+113F)

Manufacturer Information

Brand	Satco
GTIN	00045923294310
Manufacturers Part Number	S29431
UPC	045923294310



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LED PAR SHAPE LAMPS

Type LED PAR

Packaging

Carton 1

Weight 0.25

Weight Per each 0.35

Uses, Certifications, and Standards

Operating Temperature -20C (-4F) to a maximum of +45C (+113F)

standard cULus