



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## S29455 17.5W PAR38 Led 30K 40deg

Satco

Catalog Number	S29455
Manufacturer	Satco
Description	17.5 Watt PAR38 Led Lamp - 3000K - 40 Degree Beam Angle - Medium Base - 120 Volts
Weight per unit	1.5 (lbs/each)
Product Category	20210303092226

### Features

average life	25000
Base	Medium
beam angle	40
lumens	1.4k
Material	Plastic
Shape	PAR38
Warranty	3 Year Limited - 12 hr per day

### Material, Color, and Finish

color temperature	3000
Finish	Silver

### Dimensions and Weight

Size	5
------	---

### Descriptions

Description	17.5W PAR38 LED 30K 40DEG
extra long description	SATCO S29455 17.5PAR38/LED/40'/930/
Long Description	17.5 Watt PAR38 LED Lamp - 3000K - 40 Degree Beam Angle - Medium Base - 120 Volts
Product Type	17.5PAR38/Led/40'/930/120V
Special Features	Lawful for sale in California ; California T24 Compliant ; Yes - Dimmable ; Lens finish: Clear ; Warranty: 3 Year Limited - 12 hours per day ; Wet location rated ; Material: Plastic ; Incandescent Equivalent: 100W ; Enclosed Fixture Rated: Yes ; Operating Temperature: -20C (-4F) to a maximum of +45C (+113F)

### Manufacturer Information

Brand	Satco
GTIN	00045923294556
Manufacturers Part Number	S29455
UPC	045923294556



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	LED PAR

## Packaging

Carton	1
Weight	0.34
Weight Per each	1.5

## Uses, Certifications, and Standards

Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
standard	cULus