

# S29811 A19 LED

11A19/LED/3000K/1100L/120V/D

Lamp Type	LED
Bulb Type	A19
Base Type	E26
Wattage	11
Color Temperature	3000
Color Rendering Index CRI	80
Warranty	3 Year Limited



## Lighting Facts Per Bulb

<b>Brightness</b>	<b>1100 lumens</b>
<b>Estimated Energy Cost</b>	<b>\$1.32</b>
per year, based on 3 hrs/day, 11c/kWh. Energy cost depends on utility rates and light use.	
<b>Average Life</b>	<b>22.8 years</b>
Based on 3 hrs/day	
<b>Light Appearance</b>	
<b>Energy Used</b>	<b>11 watts</b>

## Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S29811	LED	*20045923298114	120	11	75	A19	Medium
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E26	11A19/LED/3000K/1100L/120V/D	Yes	n/a	4 3/8	2 3/8	1100	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
3000	Warm White	80	220	24	Box	Yes	Yes

# S29811 A19 LED

11A19/LED/3000K/1100L/120V/D

Lamp Type	LED
Bulb Type	A19
Base Type	E26
Wattage	11
Color Temperature	3000
Color Rendering Index CRI	80
Warranty	3 Year Limited



## Lighting Facts Per Bulb

<b>Brightness</b>	<b>1100 lumens</b>
<b>Estimated Energy Cost</b>	<b>\$1.32</b>
per year, based on 3 hrs/day, 11c/kWh. Energy cost depends on utility rates and light use.	
<b>Average Life</b>	<b>22.8 years</b>
Based on 3 hrs/day	
<b>Light Appearance</b>	
<b>Energy Used</b>	<b>11 watts</b>

## Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S29811	LED	*20045923298114	120	11	75	A19	Medium
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E26	11A19/LED/3000K/1100L/120V/D	Yes	n/a	4 3/8	2 3/8	1100	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
3000	Warm White	80	220	24	Box	Yes	Yes