

Project Name

Location

Prepared By

**SATCO S29825**

7A19/SW/LED/E26/27K/120V

Notes

(www) 04-09-2023 00:00:13

General

| | |
|-------------------------|--------------|
| Status | Discontinued |
| Substitute | S12419 |
| Watts | 7W |
| Incandescent Equivalent | 60W |
| Volts | 120V |
| Shape | A19 |
| Base | Medium |
| ANSI Base | E26 |
| Finish | Soft White |
| CCT (Kelvin) | 2700K |
| Temperature | Warm White |
| CRI | 80+ |
| Lumens | 800L |
| Beam Spread | 220 |
| Dimmable | Yes-Dimmable |
| Hours Rated | 15000 |
| Product Category | Type A |
| Technology | LED |

Electrical

| | |
|-----------------------|----------------------------|
| Operating Temperature | -20C (-4F) to +45C (+113F) |
|-----------------------|----------------------------|

Physical

| | |
|-----|------|
| MOL | 4.13 |
| MOD | 2.38 |

Additional Information

| | |
|----------------------------|----------------|
| Rated For Enclosed Fixture | Yes |
| Warranty | 3 Year Limited |

Compliance

| | |
|----------------------|-----------------|
| Safety Listing | cULus |
| Location Rating | Damp |
| California Status | Non-Compliant |
| Title 20 / 24 Status | Non-Compliant |
| Colorado Status | Lawful for sale |
| Hawaii Status | Lawful for sale |
| Nevada Status | Lawful for sale |
| Vermont Status | Lawful for sale |
| Washington Status | Lawful for sale |
| RoHS Compliant | Yes |
| FCC Compliant | Yes |
| SDS Sheet | LED_Lamp |