



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S29836 10W Led A19 30K *Discontinued***** *Satco*

Catalog Number	S29836
Manufacturer	Satco
Description	Satco S29836 9.8A19/Omni/220/Led/30
Weight per unit	0.1833 (lbs/each)
Product Category	Led A-Line A Shape Lamps

Features

average life	25000
connection	Medium
Fixture Type	Type A
lumens	800
Shape	A19
Voltage Rating	120
Warranty	5 Year Limited - 10 hr per day
Wattage	10

Material, Color, and Finish

Color	Frosted White
-------	---------------

Dimensions and Weight

Size	MOL: 4.19, MOD: 2.38
------	----------------------

Descriptions

Description	10W LED A19 30K ***DISCONTINUED***
Long Description	SATCO S29836 9.8A19/OMNI/220/LED/30
Product Type	9.8A19/Omni/220/Led/30K
Special Features	Dimmable: Yes Dimmable ; Operating Temp: -20C (-4F) to a maximum of +45C (+113F) ; Power Factor: 0.98 ; Safety Listing: cULus - Damp ; SDS Class: LED_Lamp ; Tested Lumens: 800

Manufacturer Information

Brand	Satco
GTIN	00045923298363
Manufacturers Part Number	S29836
sub brand	Satco
UPC	045923298363

Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS
Type	Lamps

Availability

Manufacturer Status	Inactive
---------------------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.1833

Uses, Certifications, and Standards

Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)
standard	cULus - Damp