

Project Name

Location

Prepared By



## SATCO S29837

9.8A19/OMNI/220/LED/35K

### Notes

(www) 04-14-2023 09:00:01

### General

Status	Active
Watts	9.8W
Incandescent Equivalent	60W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Frost
CCT (Kelvin)	3500K
Temperature	Neutral White
CRI	80+
Lumens	800L
Beam Spread	220
Dimmable	Yes-Dimmable
Hours Rated	25000
Product Category	Type A
Technology	LED

### Electrical

Operating Frequency	60Hz
Power Factor	0.98
Operating Temperature	-25C (-13F) to +45C (+113F)

### Physical

MOL	4.331
MOD	2.362
Housing Color	White
Weight (lb.)	0.06

### Additional Information

Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - 10 hr per day

### Compliance

Safety Listing	cULus - Certified; cULus - Listed
Location Rating	Damp
California Status	Non-Compliant
Title 20 / 24 Status	Non-Compliant
Colorado Status	Lawful for sale
Hawaii Status	Lawful for sale
Nevada Status	Lawful for sale
Vermont Status	Lawful for sale
Washington Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp