## SATCO NUVO

Project Name

ocation Prepared By



Notes

v1 04-02-2025 00:35

General		
Status	Active	
Watts	9.8W	
Incandescent Equivalent	60W	
Volts	120V	
Shape	A19	
Base	Medium	
ANSI Base	E26	
Finish	Frost	
CCT (Kelvin)	5000K	
Temperature	Natural Light	
CRI	80+	
Lumens	800L	
Beam Spread	220	
Dimmable	Yes-Dimmable	
Hours Rated	25000	
Product Category	Туре А	
Technology	LED	
Electrical		
Operating Frequency	60Hz	
Power Factor	0.98	
Operating Temperature	-25C (-13F) to +45C (+113F)	

Power Factor	0.96
Operating Temperature	-25C (-13F) to +45C (+113F)
Physical	
MOL	4.331
MOD	2.362
Housing Color	White
Weight (lb.)	0.06

Additional Information	
Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - 10 hr per day

Compliance	
Safety Listing	cULus - Certified; cULus - Listed
Location Rating	Damp
California Status	Non-Compliant
Title 20 / 24 Status	Non-Compliant
California Compliant Substitute	S8481
Colorado Status	Lawful for sale
Hawaii Status	Lawful for sale
Nevada Status	Lawful for sale
Vermont Status	Lawful for sale
Washington Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp