



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

S29925 40W Led T8 96" 50K 5500LM DBL End R17D Base

Satco

| | |
|------------------|--|
| Catalog Number | S29925 |
| Manufacturer | Satco |
| Description | 40W 8 FT. T8 Led 50K R17D Base - 50K Average Rated Hours 5500L Type B BBP Double End Wiring |
| Weight per unit | 1.2 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|------------|--------------------------------|
| Base | Recessed Double Contact HO/VHO |
| beam angle | 210 |
| lumens | 5.5k |
| Material | Glass |
| Shape | T8 |
| Warranty | 5 Year Limited - T8 LED Bulbs |

Material, Color, and Finish

| | |
|-------------------|-------|
| color temperature | 5000 |
| Finish | white |

Dimensions and Weight

| | |
|------|----|
| Size | 94 |
|------|----|

Descriptions

| | |
|------------------------|---|
| Description | 40W LED T8 96" 50K 5500LM DBL END R17D BASE |
| extra long description | SATCO S29925 40T8/LED/96-850/BP/R17 |
| Long Description | 40W 8 ft. T8 LED 50K R17d Base - 50K Average Rated Hours 5500L Type B BBP Double End Wiring |
| Product Type | 40T8/Led/96-850/BP/R17D |
| Special Features | Lawful for sale in California ; Warranty: 5 Year Limited - T8 LED Bulbs ; Fluorescent Equivalent: 110W ; DLC Approved: No ; Dimmable: Non-Dimmable ; Additional Information: Suitable for Emergency Lighting only with Satco EM Driver #S8002 ; Material: Glass ; Operating Temperature: -20C (-4F) to a maximum of +45C (+113F) ; Shatterproof: Yes ; Location Rating: Damp |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Satco |
| GTIN | 00045923299254 |
| Manufacturers Part Number | S29925 |
| UPC | 045923299254 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS |
| Type | T8 |

Packaging

| | |
|-----------------|-------|
| Carton | 10 |
| Weight | 0.88 |
| Weight Per each | 1.187 |

Uses, Certifications, and Standards

| | |
|-----------------------|---|
| Operating Temperature | -20C (-4F) to a maximum of +45C (+113F) |
| standard | cULus |