



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

S29925 40W Led T8 96" 50K 5500LM DBL End R17D Base

Satco

Catalog Number	S29925
Manufacturer	Satco
Description	40W 8 FT. T8 Led 50K R17D Base - 50K Average Rated Hours 5500L Type B BBP Double End Wiring
Weight per unit	1.2 (lbs/each)
Product Category	Lighting

Features

Base	Recessed Double Contact HO/VHO
beam angle	210
lumens	5.5k
Material	Glass
Shape	T8
Warranty	5 Year Limited - T8 LED Bulbs

Material, Color, and Finish

color temperature	5000
Finish	white

Dimensions and Weight

Size	94
------	----

Descriptions

Description	40W LED T8 96" 50K 5500LM DBL END R17D BASE
extra long description	SATCO S29925 40T8/LED/96-850/BP/R17
Long Description	40W 8 ft. T8 LED 50K R17d Base - 50K Average Rated Hours 5500L Type B BBP Double End Wiring
Product Type	40T8/Led/96-850/BP/R17D
Special Features	Lawful for sale in California ; Warranty: 5 Year Limited - T8 LED Bulbs ; Fluorescent Equivalent: 110W ; DLC Approved: No ; Dimmable: Non-Dimmable ; Additional Information: Suitable for Emergency Lighting only with Satco EM Driver #S8002 ; Material: Glass ; Operating Temperature: -20C (-4F) to a maximum of +45C (+113F) ; Shatterproof: Yes ; Location Rating: Damp

Manufacturer Information

Brand	Satco
GTIN	00045923299254
Manufacturers Part Number	S29925
UPC	045923299254



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
Type	T8

Packaging

Carton	10
Weight	0.88
Weight Per each	1.187

Uses, Certifications, and Standards

Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
standard	cULus