



S3105

500T3Q/CL
500 watt; Halogen; T3; Clear; 1500 Average rated Hours; 9500 Lumens; Double Ended base; 120 volts



Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output

S3105

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S3105	045923031052	500	T3	Double Ended	R7s	500T3Q/CL	120
Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Kelvin Temp	Color	Average Rated Hours
Clear	4 11/16"	0.38"	C-8	9500	2900	Warm White	1500
Pack	Package Type	RoHS Compliant					
480/12	Box	Yes					



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S3105

500T3Q/CL
500 watt; Halogen; T3; Clear; 1500 Average rated Hours; 9500 Lumens; Double Ended base; 120 volts



Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output

S3105

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S3105	045923031052	500	T3	Double Ended	R7s	500T3Q/CL	120
Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Kelvin Temp	Color	Average Rated Hours
Clear	4 11/16"	0.38"	C-8	9500	2900	Warm White	1500
Pack	Package Type	RoHS Compliant					
480/12	Box	Yes					



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

