



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S3713BK Recept Recessed 15A/125V BK W/Wallplate

Pass & Seymour/Legrand

Catalog Number	S3713BK
Manufacturer	Pass & Seymour/Legrand
Description	Clock Hanger Recessed Receptacle With Smooth Wall Plate 15A, 125V, Gray
Weight per unit	0.2760 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	15
indoor/outdoor	Indoor
media	Yes
Number of Wires	3
Outlet Type	Commercial, Indoor
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wire Size	14 - 10

Dimensions and Weight

Size	5"
------	----

Descriptions

Description	RECP RECESSED 15A/125V BK W/WALLPLATE
extra long description	P&S S3713BK RECEPT RECESSED 15A/125
Long Description	Clock Hanger Recessed Receptacle with Smooth Wall Plate 15A, 125V, Gray
Product Type	Recept Recessed 15A/125V BK W/Plate
Special Features	Dust & moisture resistant, clock hanger receptacle, cellular neoprene sealing mat fits under wall plate

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007687811
Manufacturers Part Number	S3713-BK
UPC	785007687811

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Outlet

Trade Size

Amperage	15.0
----------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	50
Weight Per each	0.276

Uses, Certifications, and Standards

Application	Commercial
Mounting	WALL
nema rating	5-15R
standard	CULUS, UL 498