



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S38946 100W Led Temp Light 5K Integrated Cord/Plug & Hook

Satco

Catalog Number	S38946
Manufacturer	Satco
Description	100 Watt Led Hi-Lumen Temporary Hi-Bay Caged Lamp - 5000K - Integrated Cord / Plug & Hook - 120 Volts
Weight per unit	5.3 (lbs/each)
Product Category	Lighting

Features

average life	50000
Base	Plug 3-Prong
beam angle	360
lumens	10k
Material	Plastic; Steel
Shape	Corncob
Voltage Rating	120
Warranty	5 Year Limited - Hi-Pro
Wattage	100

Material, Color, and Finish

Finish	ORANGE
--------	--------

Dimensions and Weight

Size	10.9
------	------

Descriptions

Description	100W LED TEMP LIGHT 5K INTEGRATED CORD/PLUG & HOOK
extra long description	SATCO S38946 100W/LED/HID/TEMP/5K/1
Long Description	100 Watt LED Hi-Lumen Temporary Hi-Bay Caged Lamp - 5000K - Integrated Cord / Plug & Hook - 120 Volts
Product Type	100W/Led/Hid/Temp/5K/120V
Special Features	Lawful for sale in California ; Color Temperature: Natural Light ; Weight: 3.65 lb. ; DLC Approved: No ; CEC Title 24: No ; Energy Star: No ; Warranty: 5 Year Limited - Hi-Pro ; FCC Compliant: Yes ; Proposition 65: No ; Incandescent Equivalent: 400W ; Indoor/Outdoor Rated: Indoor ; Lens Finish: Frosted ; Operating Temperature: -30C (-22F) to a maximum of +60C (+140F)

Manufacturer Information

Brand	Satco
GTIN	00045923389467
Manufacturers Part Number	S38946
UPC	045923389467



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Led Lighting
Type	HID Replacements

Packaging

Carton	1
Package	4
Weight	3.65
Weight Per each	5.28

Uses, Certifications, and Standards

Operating Temperature	-30C (-22F) to a maximum of +60C (+140F)
standard	cULus