



S3912

15T6/145V
15 watt T6 Incandescent; Clear; 2000 average rated hours; 90 lumens; Candelabra base; 145 volts

Features

- Special application incandescent
- 145 volt



S3912

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S3912	045923039126	15	T6	Candelabra	E12	15T6/145V	145

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Clear	3 1/16"	0.75"	C-5A	90	2000	120	Sleeve/10

RoHS Compliant
Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S3912

15T6/145V
15 watt T6 Incandescent; Clear; 2000 average rated hours; 90 lumens; Candelabra base; 145 volts

Features

- Special application incandescent
- 145 volt



S3912

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S3912	045923039126	15	T6	Candelabra	E12	15T6/145V	145

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Clear	3 1/16"	0.75"	C-5A	90	2000	120	Sleeve/10

RoHS Compliant
Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

