



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S39390 18W Led Hid RPLCMT 50K 1P

Satco

Catalog Number	S39390
Manufacturer	Satco
Description	Satco S39390 18W/Led/Hid/5000K/100-
Weight per unit	0.9458 (lbs/each)
Product Category	Led Specialty Lamps & Modules

Features

average life	50000
Base	Medium
beam angle	300
dimmable	No
lumens	2.52k
Material	Plastic; Aluminum
Shape	Corncob
surge protection	Built-in surge protection - 2.5KV
Voltage Rating	277
Warranty	5 Year Limited - Hi-Pro
Wattage	18

Material, Color, and Finish

color temperature	5000
-------------------	------

Dimensions and Weight

Diameter	2.38
Length	5.69

Descriptions

Description	18W LED HID RPLCMT 50K 1P
Long Description	SATCO S39390 18W/LED/HID/5000K/100-
Product Type	18W/Led/Hid/5000K/100-277V/E26
Special Features	Warranty: 5 Year Limited ; Country of origin: China ; IP65 rated: Yes ; CEC: Non-Compliant ; Operating Temp: -20C (-4F) to a maximum of +40C (+104F) ; Safety Listing: cULus - Listed ; Beam spread: 300 degrees ; Burning position: Universal ; Color temp: Natural Light ; Incandescent equivalent: 120W ; Fluorescent equivalent: 32W ; HID equivalent: 70W ; Voltage:100-277V



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Satco
GTIN	00045923303906
Manufacturers Part Number	S39390
sub brand	Satco
UPC	045923303906

Taxonomies, Classifications, and Categories

Category Description	LED SPECIALTY LAMPS & MODULES
Type	HID Replacements

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Weight	0.66
Weight Per each	0.9458

Uses, Certifications, and Standards

Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)
-----------------------	--