



S3942

60A19/CL/VS
60 watt A19 Incandescent; Clear; 2500 average rated hours;
580 lumens; Medium base; 130 volts; 2/Pack

Features

- General Service Incandescent
- Household or Commercial use
- Vibration Service
- Long Life
- 130 volt



S3942

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S3942	045923039423	60	A19	Medium	E26	60A19/CL/VS	130

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Clear	4 1/8"	2.38"	C-9	580	2500	120	2pk

RoHS Compliant
Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S3942

60A19/CL/VS
60 watt A19 Incandescent; Clear; 2500 average rated hours;
580 lumens; Medium base; 130 volts; 2/Pack

Features

- General Service Incandescent
- Household or Commercial use
- Vibration Service
- Long Life
- 130 volt



S3942

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S3942	045923039423	60	A19	Medium	E26	60A19/CL/VS	130

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Clear	4 1/8"	2.38"	C-9	580	2500	120	2pk

RoHS Compliant
Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

