



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## S39597 9.5W Led A19 50K (4PK) Non-Dimming

Satco

Catalog Number	S39597
Manufacturer	Satco
Description	9.5W - A19 Led - Frosted - 5000K - Medium Base - 220 Degree Beam Angle - 120V - Non-Dimmable - 4PK
Weight per unit	0.5800 (lbs/each)
Product Category	Lighting

### Features

average life	15000
Base	Medium
beam angle	220
lumens	800
Material	Plastic; Metal; Electronic Components
Shape	A19
Warranty	3 Year Limited - 10 hr per day

### Material, Color, and Finish

color temperature	5000
Finish	Frosted

### Dimensions and Weight

Size	4.33
------	------

### Descriptions

Description	9.5W LED A19 50K (4PK) NON-DIMMING
extra long description	SATCO S39597 9.5A19/LED/850/ND/120V
Long Description	9.5W - A19 LED - Frosted - 5000K - Medium Base - 220 Degree Beam Angle - 120V - Non-Dimmable - 4PK
Product Type	9.5A19/Led/850/ND/120V/4PK
Special Features	Watts: 9.5 ; Warranty: 3 Year Limited - 10 hours per day ; ANSI Base: E26 ; CEC: Unavailable for sale in California ; Enclosed Rated Lamp ; Material: Plastic - Metal - Electronic Components ; Incandescent Equivalent: 60W ; Location Rating: Damp ; Operating Temperature: -25C (-13F) to a maximum of +45C (+113F) ; Non-Dimmable

### Manufacturer Information

Brand	Satco
GTIN	00045923395970
Manufacturers Part Number	S39597
UPC	045923395970



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description LED A-LINE SHAPE LAMPS

Type Type A

## Packaging

Carton 1

Weight 0.09

Weight Per each 0.58

## Uses, Certifications, and Standards

Operating Temperature -20C (-4F) to a maximum of +45C (+113F)

standard cULus