



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S39751 40W Led Hid RPL (Adj LT PNLS)

Satco

Catalog Number	S39751
Manufacturer	Satco
Description	40 Watt Led Hid Replacement - 5000K - Mogul Extended Base - Adjustable Beam Angle - 100-277 Volts
Weight per unit	2.2 (lbs/each)
Product Category	Lighting

Features

average life	50000
Base	EX39
beam angle	260
lumens	5.6k
Material	Thermo Plastic (PBT); Steel; Aluminum
Shape	ED28
surge protection	Built-in surge protection - 4KV
voltage range	277
Warranty	5 Year Limited - Hi-Pro
Wattage	40

Material, Color, and Finish

color temperature	5000
Finish	Clear

Dimensions and Weight

Size	7.24
------	------

Descriptions

Description	40W LED HID RPL (ADJ LT PNLS)
extra long description	SATCO S39751 40W/LED/HID/MB-G3/50K/
Long Description	40 Watt LED HID Replacement - 5000K - Mogul Extended Base - Adjustable Beam Angle - 100-277 Volts
Product Type	40W/Led/Hid/MB-G3/50K/100-277V
Special Features	Lawful for sale in California ; Color Temperature: Natural Light ; Dimmable: Non-Dimmable ; Lamp Base: Mogul Extended ; MOL: 7.24 in. ; MOD: 3.35 in. ; Weight: 1.85 lb. ; DLC Approved

Manufacturer Information

Brand	Satco
GTIN	00045923397516
Manufacturers Part Number	S39751
UPC	045923397516



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED SPECIALTY LAMPS & MODULES
Type	LED HID Replacement

Packaging

Carton	6
Package	12
Weight	1.85
Weight Per each	2.17

Uses, Certifications, and Standards

Operating Temperature	-20C (-4F) to a maximum of +65C (+149F)
standard	cULus Classified