



S4881

40A15/TF
40 watt A15 Incandescent; Frost; 2500 average rated hours;
265 lumens; Medium base; 130 volts; Shatter Proof

Features

- Shatterproof coated incandescent
- Vibration service
- Long life
- Brass Base
- 130 volt



S4881

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S4881	045923048814	40	A15	Medium	E26	40A15/TF	130

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Frost Shatter Proof	3 1/2"	1.88"	C-9	265	2500	500/25	Box

RoHS Compliant
Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S4881

40A15/TF
40 watt A15 Incandescent; Frost; 2500 average rated hours;
265 lumens; Medium base; 130 volts; Shatter Proof

Features

- Shatterproof coated incandescent
- Vibration service
- Long life
- Brass Base
- 130 volt



S4881

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S4881	045923048814	40	A15	Medium	E26	40A15/TF	130

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Frost Shatter Proof	3 1/2"	1.88"	C-9	265	2500	500/25	Box

RoHS Compliant							
Yes							



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

