



S4998

250R40/HR
250 watt R40 Incandescent; Red Heat; 6000 average rated hours; Medium base; 120 volts

Features

- General Service Reflector
- Household or Commercial use
- Long Life
- Brass Base



S4998

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S4998	045923049989	250	R40	Medium	E26	250R40/HR	120

Finish	MOL In Inches	MOD In Inches	Filament	Average Rated Hours	Pack	Package Type	RoHS Compliant
Red Heat	6 1/2"	5.00"	C-9	6000	12	Sleeve	Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S4998

250R40/HR
250 watt R40 Incandescent; Red Heat; 6000 average rated hours; Medium base; 120 volts

Features

- General Service Reflector
- Household or Commercial use
- Long Life
- Brass Base



S4998

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S4998	045923049989	250	R40	Medium	E26	250R40/HR	120

Finish	MOL In Inches	MOD In Inches	Filament	Average Rated Hours	Pack	Package Type	RoHS Compliant
Red Heat	6 1/2"	5.00"	C-9	6000	12	Sleeve	Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

