



S5829

MH175/ED28/U/4K
175 watt; Metal Halide HID; Mogul base; ED28; Clear; 65 CRI;
4200K

Features

- Uniform light distribution
- Superior performance
- High Efficiency



S5829

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S5829	045923058295	175	ED28	Mogul	E39	M57/E	MH175/ED28/U/4K
Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Color	Probe Start
Clear	8.31"	3.50"	10000	13600	4200	Cool White	Yes
Pack	Package Type	CRI	Burning Position	RoHS Compliant			
12	Box	65	Universal	Yes			



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S5829

MH175/ED28/U/4K
175 watt; Metal Halide HID; Mogul base; ED28; Clear; 65 CRI;
4200K

Features

- Uniform light distribution
- Superior performance
- High Efficiency



S5829

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S5829	045923058295	175	ED28	Mogul	E39	M57/E	MH175/ED28/U/4K
Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Color	Probe Start
Clear	8.31"	3.50"	10000	13600	4200	Cool White	Yes
Pack	Package Type	CRI	Burning Position	RoHS Compliant			
12	Box	65	Universal	Yes			



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

