



# S5843

MH400/ED28/U/4K/E39  
400 watt; Metal Halide HID; Mogul base; ED28; Clear; 65 CRI;  
4200K

### Features

- Uniform light distribution
- Superior performance
- High Efficiency



S5843

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S5843	045923058431	400	ED28	Mogul	E39	M59/E	MH400/ED28/U/4K/E39

  

Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Color	Probe Start
Clear	8.31"	3.50"	20000	36000	4200	Cool White	Yes

  

Pack	Package Type	CRI	Burning Position	RoHS Compliant
12	Box	65	Universal	Yes



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S5843

MH400/ED28/U/4K/E39  
400 watt; Metal Halide HID; Mogul base; ED28; Clear; 65 CRI;  
4200K

### Features

- Uniform light distribution
- Superior performance
- High Efficiency



S5843

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S5843	045923058431	400	ED28	Mogul	E39	M59/E	MH400/ED28/U/4K/E39
Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Color	Probe Start
Clear	8.31"	3.50"	20000	36000	4200	Cool White	Yes
Pack	Package Type	CRI	Burning Position	RoHS Compliant			
12	Box	65	Universal	Yes			



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

