



S5845

MH1000/BT37/U/4K
1000 watt; Metal Halide HID; Mogul base; BT37; Clear; 65 CRI;
4200K

Features

- Uniform light distribution
- Superior performance
- High Efficiency



S5845

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S5845	045923058455	1000	BT37	Mogul	E39	M47/E	MH1000/BT37/U/4K
Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Color	Probe Start
Clear	11.5"	4.63"	15000	110000	4200	Cool White	Yes
Pack	Package Type	CRI	Burning Position	RoHS Compliant			
12	Box	65	Universal	Yes			



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S5845

MH1000/BT37/U/4K
1000 watt; Metal Halide HID; Mogul base; BT37; Clear; 65 CRI;
4200K

Features

- Uniform light distribution
- Superior performance
- High Efficiency



S5845

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S5845	045923058455	1000	BT37	Mogul	E39	M47/E	MH1000/BT37/U/4K
Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Color	Probe Start
Clear	11.5"	4.63"	15000	110000	4200	Cool White	Yes
Pack	Package Type	CRI	Burning Position	RoHS Compliant			
12	Box	65	Universal	Yes			



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

