



S5862

MP175/ED17/U
175 watt; Metal Halide HID; Medium base; ED17; Clear; 65
CRI; 4000K

Features

- Uniform light distribution
- Superior performance
- High Efficiency
- Open Rated



S5862

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S5862	045923058622	175	ED17	Medium	E26	M57/O	MP175/ED17/U
Finish	MOL In Inches	MOL in mm	Initial Lumens	Average Rated Hours	Kelvin Temp	CRI	Burning Position
Clear	5.44"	138.18 mm	14000	12000	4000	65	Universal
Open Rated						Pack	
Yes						12	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S5862

MP175/ED17/U
175 watt; Metal Halide HID; Medium base; ED17; Clear; 65
CRI; 4000K

Features

- Uniform light distribution
- Superior performance
- High Efficiency
- Open Rated



S5862

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S5862	045923058622	175	ED17	Medium	E26	M57/O	MP175/ED17/U
Finish	MOL In Inches	MOL in mm	Initial Lumens	Average Rated Hours	Kelvin Temp	CRI	Burning Position
Clear	5.44"	138.18 mm	14000	12000	4000	65	Universal
Open Rated						Pack	
Yes						12	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

