



S5884

MP400/ED37 /PS /BU /4K
400 watt; Metal Halide HID; Mogul base; ED37; Clear; 65 CRI;
4200K

Features

- Uniform light distribution
- Superior performance
- High Efficiency
- Pulse Start
- Open Rated



S5884

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S5884	045923058844	400	ED37	Mogul	E39	M155/O	MP400/ED37 /PS /BU /4K
Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Color	Pulse Start
Clear	11.5"	4.63"	20000	42000	4200	Cool White	Yes
Open Rated	Pack	Package Type	CRI	Burning Position	RoHS Compliant		
Yes	12	Box	65	BU±15'	Yes		



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S5884

MP400/ED37 /PS /BU /4K
400 watt; Metal Halide HID; Mogul base; ED37; Clear; 65 CRI;
4200K

Features

- Uniform light distribution
- Superior performance
- High Efficiency
- Pulse Start
- Open Rated



S5884

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S5884	045923058844	400	ED37	Mogul	E39	M155/O	MP400/ED37 /PS /BU /4K
Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Color	Pulse Start
Clear	11.5"	4.63"	20000	42000	4200	Cool White	Yes
Open Rated	Pack	Package Type	CRI	Burning Position	RoHS Compliant		
Yes	12	Box	65	BU±15'	Yes		



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

