



S6237

13T2/50
 13 watt; Mini Spiral Compact Fluorescent; 5000K; 82 CRI;
 Medium base; 120 volts; 4-pack

Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On
- 4-Bulb Value Pack



S6237

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Incandescent Equivalent
S6237	045923062377	13	T2	Medium	E26	13T2/50	60W

Voltage	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
120	4.13"	1.81"	880	12000	5000	Natural Light	12

Package Type	CRI	ENERGY STAR	RoHS Compliant	UL Listed
Box	82	ENERGY STAR	Yes	Yes



National Toll-Free:
 800.43.SATCO
 (800.437.2826)
 www.satco.com

Distribution Centers:
 New York, Florida, Texas,
 Washington, California,
 Puerto Rico

Corporate Offices:
 110 Heartland Blvd.,
 Brentwood, NY 11717
 800.437.2826 631.243.2022
 Fax 631.243.2027





S6237

13T2/50
 13 watt; Mini Spiral Compact Fluorescent; 5000K; 82 CRI;
 Medium base; 120 volts; 4-pack

Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On
- 4-Bulb Value Pack



S6237

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Incandescent Equivalent
S6237	045923062377	13	T2	Medium	E26	13T2/50	60W

Voltage	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
120	4.13"	1.81"	880	12000	5000	Natural Light	12

Package Type	CRI	ENERGY STAR	RoHS Compliant	UL Listed
Box	82	ENERGY STAR	Yes	Yes



National Toll-Free:
 800.43.SATCO
 (800.437.2826)
 www.satco.com

Distribution Centers:
 New York, Florida, Texas,
 Washington, California,
 Puerto Rico

Corporate Offices:
 110 Heartland Blvd.,
 Brentwood, NY 11717
 800.437.2826 631.243.2022
 Fax 631.243.2027

