



S7007

500BR40FL/POOL
500 watt BR40 Incandescent; Frost; 2000 average rated hours;
5500 lumens; Medium base; 130 volts

Features

- Pool Lamp
- Brass base prevents freezing in the socket
- Heat resistant glass
- 130 volts



S7007

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S7007	045923070075	500	BR40	Medium	E26	500BR40FL/POOL	130

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Frosted	6 1/2"	5.00"	CC-9/1	5500	2000	24/12	Box

RoHS Compliant
Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S7007

500BR40FL/POOL
500 watt BR40 Incandescent; Frost; 2000 average rated hours;
5500 lumens; Medium base; 130 volts

Features

- Pool Lamp
- Brass base prevents freezing in the socket
- Heat resistant glass
- 130 volts



S7007

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S7007	045923070075	500	BR40	Medium	E26	500BR40FL/POOL	130

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Frosted	6 1/2"	5.00"	CC-9/1	5500	2000	24/12	Box

RoHS Compliant
Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

