



S7217

13T2/27
13 watt; Mini Spiral Compact Fluorescent; 2700K; 82 CRI;
Medium base; 120 volts

Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On



S7217

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S7217	045923072178	120	13	60W	T2	Medium	E26
Lamp Code	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
13T2/27	4.13"	1.81"	900	12000	2700	Warm White	48/12
Package Type	CRI	CEC Status	Hg Content	RoHS Compliant	UL or ETL Listed	Warranty	
Box	82	Lawful for sale in California	1.6 mg	Yes	Yes	2 Year Limited	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S7217

13T2/27
13 watt; Mini Spiral Compact Fluorescent; 2700K; 82 CRI;
Medium base; 120 volts

Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On



S7217

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S7217	045923072178	120	13	60W	T2	Medium	E26
Lamp Code	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
13T2/27	4.13"	1.81"	900	12000	2700	Warm White	48/12
Package Type	CRI	CEC Status	Hg Content	RoHS Compliant	UL or ETL Listed	Warranty	
Box	82	Lawful for sale in California	1.6 mg	Yes	Yes	2 Year Limited	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

