



S7228

23T2/41
23 watt; Mini Spiral Compact Fluorescent; 4100K; 82 CRI;
Medium base; 120 volts

Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On



S7228

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S7228	045923072284	120	23	100W	T2	Medium	E26

Lamp Code	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
23T2/41	4.88"	2.13"	1600	12000	4100	Cool White	48/12

CRI	CEC Status	Hg Content	RoHS Compliant	UL or ETL Listed	Warranty
82	Lawful for sale in California	1.6 mg	Yes	Yes	2 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S7228

23T2/41
23 watt; Mini Spiral Compact Fluorescent; 4100K; 82 CRI;
Medium base; 120 volts

Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On



S7228

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S7228	045923072284	120	23	100W	T2	Medium	E26

Lamp Code	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
23T2/41	4.88"	2.13"	1600	12000	4100	Cool White	48/12

CRI	CEC Status	Hg Content	RoHS Compliant	UL or ETL Listed	Warranty
82	Lawful for sale in California	1.6 mg	Yes	Yes	2 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

