



# S7242

23R40/41  
23 watt; R40 Compact Fluorescent; 4100K; 82 CRI; Medium base; 120 volts

### Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On



S7242

| Item Number  | UPC           | Watts          | Lamp Shape     | Base                | ANSI Base   | Lamp Code  | Incandescent Equivalent |
|--------------|---------------|----------------|----------------|---------------------|-------------|------------|-------------------------|
| S7242        | 045923072420  | 23             | R40            | Medium              | E26         | 23R40/41   | 85W                     |
| Voltage      | MOL In Inches | MOD In Inches  | Initial Lumens | Average Rated Hours | Kelvin Temp | Color      | Pack                    |
| 120          | 6.49"         | 5.00"          | 1090           | 10000               | 4100        | Cool White | 24/6                    |
| Package Type | CRI           | RoHS Compliant | UL Listed      |                     |             |            |                         |
| Box          | 82            | Yes            | Yes            |                     |             |            |                         |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S7242

23R40/41  
23 watt; R40 Compact Fluorescent; 4100K; 82 CRI; Medium base; 120 volts

### Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On



S7242

| Item Number  | UPC           | Watts          | Lamp Shape     | Base                | ANSI Base   | Lamp Code  | Incandescent Equivalent |
|--------------|---------------|----------------|----------------|---------------------|-------------|------------|-------------------------|
| S7242        | 045923072420  | 23             | R40            | Medium              | E26         | 23R40/41   | 85W                     |
| Voltage      | MOL In Inches | MOD In Inches  | Initial Lumens | Average Rated Hours | Kelvin Temp | Color      | Pack                    |
| 120          | 6.49"         | 5.00"          | 1090           | 10000               | 4100        | Cool White | 24/6                    |
| Package Type | CRI           | RoHS Compliant | UL Listed      |                     |             |            |                         |
| Box          | 82            | Yes            | Yes            |                     |             |            |                         |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

