



S7242

23R40/41
23 watt; R40 Compact Fluorescent; 4100K; 82 CRI; Medium base; 120 volts

Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On



S7242

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Incandescent Equivalent
S7242	045923072420	23	R40	Medium	E26	23R40/41	85W
Voltage	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
120	6.49"	5.00"	1090	10000	4100	Cool White	24/6
Package Type	CRI	RoHS Compliant	UL Listed				
Box	82	Yes	Yes				



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S7242

23R40/41
23 watt; R40 Compact Fluorescent; 4100K; 82 CRI; Medium base; 120 volts

Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On



S7242

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Incandescent Equivalent
S7242	045923072420	23	R40	Medium	E26	23R40/41	85W
Voltage	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
120	6.49"	5.00"	1090	10000	4100	Cool White	24/6
Package Type	CRI	RoHS Compliant	UL Listed				
Box	82	Yes	Yes				



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

