



# S7247

15R30/27  
15 watt; R30 Compact Fluorescent; 2700K; 82 CRI; Medium base; 120 volts

### Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On



S7247

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Incandescent Equivalent
S7247	045923072475	15	R30	Medium	E26	15R30/27	65W
Voltage	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
120	5.39"	3.75"	700	10000	2700	Warm White	24/6
Package Type	CRI	ENERGY STAR	RoHS Compliant	UL Listed			
Box	82	ENERGY STAR	Yes	Yes			



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S7247

15R30/27  
15 watt; R30 Compact Fluorescent; 2700K; 82 CRI; Medium base; 120 volts

### Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On



S7247

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Incandescent Equivalent
S7247	045923072475	15	R30	Medium	E26	15R30/27	65W
Voltage	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
120	5.39"	3.75"	700	10000	2700	Warm White	24/6
Package Type	CRI	ENERGY STAR	RoHS Compliant	UL Listed			
Box	82	ENERGY STAR	Yes	Yes			



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

