



S7376

105T5/41
105 watt; T5 Compact Fluorescent; 4100K; 85 CRI; Medium base; 120 volts

Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On



S7376

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S7376	045923073762	120	105	400W	T5	Medium	E26
Lamp Code	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
105T5/41	10-3/4"	4.31"	7000	10000	4100	Cool White	12/6
Package Type	CRI	CEC Status	Hg Content	RoHS Compliant	UL or ETL Listed	Warranty	
Box	85	Lawful for sale in California	4.8 mg	Yes	Yes	2 Year Limited	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S7376

105T5/41
105 watt; T5 Compact Fluorescent; 4100K; 85 CRI; Medium base; 120 volts

Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On



S7376

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S7376	045923073762	120	105	400W	T5	Medium	E26
Lamp Code	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
105T5/41	10-3/4"	4.31"	7000	10000	4100	Cool White	12/6
Package Type	CRI	CEC Status	Hg Content	RoHS Compliant	UL or ETL Listed	Warranty	
Box	85	Lawful for sale in California	4.8 mg	Yes	Yes	2 Year Limited	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

