



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S803UK50 MCB S800 3P K 50a

Industrial Connections &

Catalog Number	S803UK50
Manufacturer	Industrial Connections &
Description	High Performance Miniature Circuit Breaker With Cage Terminal, Rated Current 50 Amps, 3 Pole, Trip Curve K, Voltage Up to 240 Vac, Ultimate Short-Circuit Breaking Capacity 50 Ka, IEC/En 60947-2, UI 489, Csa 22.2 No. 5-02
Weight per unit	1,700.0 (lbs/each)
Product Category	3 Pole Din Rail Mount Circuit

Features

amperage rating	50 W
interrupt rating	50 kA
Poles	3 kW
Trip Type	OUTSIDE CORNER FITTING, OUTSIDE CORNER FITTING TYPE; ABS PLASTIC MATERIAL; 1.5 INCH L X 0.91 INCH W X 0.6 INCH H SIZE; WHITE FINISH; PAN-WAY LD10 SERIES NON-METALLIC SURFACE RACEWAY USED ON; UL, CE APPROVAL; 10 STANDARD PACKAGE; PAN-WAY[R] BRAND
Voltage Rating	240 W

Dimensions and Weight

Height	95 Millimeters
Length	88.5 Millimeters
Width	79.5 Millimeters

Descriptions

Description	MCB S800 3P K 50A
extra long description	ABB S803U-K50 MCB S800 3P K 50A
Long Description	High Performance Miniature Circuit Breaker with Cage Terminal, Rated Current 50 Amps, 3 Pole, Trip Curve K, Voltage up to 240 VAC, Ultimate Short-Circuit Breaking Capacity 50 kA, IEC/EN 60947-2, UL 489, CSA 22.2 No. 5-02
Product Type	MCB S800 3P K 50a
Special Features	UL current limiting

Manufacturer Information

Brand	ABB
GTIN	00804325372312
Manufacturers Part Number	S803U-K50
UPC	804325372312



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	Miniature circuit breakers

Packaging

Carton	1
Weight Per each	1700

Uses, Certifications, and Standards

Application	For use as branch protection
Frequency Rating	50/60 Hz
Operating Temperature	-25 to +60 Degrees Celcius
standard	UL mA