

Eaton S811+T30P3S

Catalog Number: S811+T30P3S

Eaton S811+ soft starter, Soft Starter 200MM 304 A Pump control with OPT Inside delta



Photo is representative

General specifications

Product Name	Catalog Number
Eaton S811+ soft starter	S811+T30P3S
UPC	Product Length/Depth
786685559025	19 in
Product Height	Product Width
12.5 in	14.5 in
Product Weight	Compliances
45 lb	CE Marked

Certifications

IEC 60947-4-2
EN 60947-4-2
UL Listed
CSA Certified
CSA Certified for Elevator Duty
UL Recognized
CSA file No. 3211-06

Product specifications

Amperage Rating

95-304A

Special features

30 second ramp or 450% current limit at 50°C, inside-the-delta connection, pump control and extended ramp functions

Type

Premium

Frame size

T

Rating

90 kW at 230 V, 160 kW at 380-400 V, 185 kW at 440 V

Resources

Application notes

[S8x1 adjustment - Switching from S801+ to S811+](#)

Catalogs

[Product Range Catalog Drives Engineering](#)

Multimedia

[Soft Starter DS7 up to 32 A](#)

[Soft starter DS7 up to 200 A](#)

[Soft Starter Product Family Overview](#)

Specifications and datasheets

[Eaton Specification Sheet - S811+T30P3S](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)