

# Specifications



Photo is representative



## Eaton S811+T30P3S

Eaton S811+ soft starter, Soft Starter 200MM 304 A Pump control with OPT Inside delta

### General specifications

<b>PRODUCT NAME</b>	Eaton S811+ soft starter
<b>CATALOG NUMBER</b>	S811+T30P3S
<b>UPC</b>	786685559025
<b>PRODUCT LENGTH/DEPTH</b>	19 in
<b>PRODUCT HEIGHT</b>	12.5 in
<b>PRODUCT WIDTH</b>	14.5 in
<b>PRODUCT WEIGHT</b>	45 lb
<b>COMPLIANCES</b>	CE Marked
<b>CERTIFICATIONS</b>	IEC 60947-4-2 EN 60947-4-2 UL Listed CSA Certified CSA Certified for Elevator Duty UL Recognized CSA file No. 3211-06

## Product specifications

AMPERAGE RATING	95-304A
SPECIAL FEATURES	30 second ramp or 450% current limit at 50°C, inside-the-delta connection, pump control and extended ramp functions
TYPE	Premium
FRAME SIZE	T
RATING	90 kW at 230 V, 160 kW at 380-400 V, 185 kW at 440 V

## Resources

APPLICATION NOTES	<a href="#">S8x1 adjustment - Switching from S801+ to S811+</a>
CATALOGS	<a href="#">Product Range Catalog Drives Engineering</a>
MULTIMEDIA	<a href="#">Soft Starter Product Family Overview</a> <a href="#">Soft Starter DS7 up to 32 A</a> <a href="#">Soft starter DS7 up to 200 A</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - S811+T30P3S</a>
WARRANTY GUIDES	<a href="#">Selling Policy 25-000 - Distribution and Control Products and Services</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

