

# Eaton S811 T30P3S

Catalog Number: S811+T30P3S

Eaton S811+ soft starter, Soft Starter 200MM 304 A Pump control with OPT Inside delta



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton S811+ soft starter	S811+T30P3S
UPC	Product Length/Depth
786685559025	19 in
Product Height	Product Width
12.5 in	14.5 in
Product Weight	Compliances
45 lb	CE Marked

## Certifications

IEC 60947-4-2  
EN 60947-4-2  
UL Listed  
CSA Certified  
CSA Certified for Elevator Duty  
UL Recognized  
CSA file No. 3211-06

**Amperage Rating**

95-304A

**Special features**

30 second ramp or 450% current limit at 50°C, inside-the-delta connection, pump control and extended ramp functions

**Type**

Premium

**Frame size**

T

**Rating**

90 kW at 230 V, 160 kW at 380-400 V, 185 kW at 440 V

**Application notes**

S8xL adjustment - Switching from S801+ to S811+

**Brochures**

S811+/S801+ soft starters

**Catalogs**

Product Datasheet - S811+T30P3S

Product Range Catalog Drives Engineering

Eaton's Volume 6—Solid-State Motor Control

**Drawings**

Type S811+ Soft Starter - T-frame

**Installation instructions**

Instructions for S811+ Soft Starter, S811+T..., S811+U..., and S811+V

**Multimedia**

Soft starter DS7 up to 200 A

Soft Starter DS7 up to 32 A

Soft Starter Product Family Overview

**Specifications and datasheets**

Eaton Specification Sheet - S811+T30P3S

**Warranty guides**

Selling Policy 25-000 - Distribution and Control Products and Services