

# Eaton S811 V36N3S

Catalog Number: S811+V36N3S

Eaton S811+ soft starter, Non-combination Soft Starter, Frame size 290 mm, 360 A, 600 V, Three-pole

## General specifications



Photo is representative

### Product Name

Eaton S811+ soft starter

### Catalog Number

S811+V36N3S

### UPC

786685559094

### Product Length/Depth

16.57 in

### Product Height

7.35 in

### Product Width

11.05 in

### Product Weight

48 lb

### Compliances

CE Marked

### Certifications

IEC 60947-4-2

EN 60947-4-2

UL Listed

CSA Certified

## defaultTaxonomyAttributeLabel

### Amperage Rating

360A

### Number Of Poles

Three-pole

### Type

Soft starter

### Voltage rating

600 V

### Frame size

290 mm

## Resources

### Application notes

S8x1 adjustment - Switching from S801+ to S811+

### Brochures

S811+/S801+ soft starters

### Catalogs

Eaton's Volume 6—Solid-State Motor Control

Product Range Catalog Drives Engineering

Product Datasheet - S811+V36N3S

### Drawings

Type S811+ Soft Starter - V-frame

### Installation instructions

Instructions for S811+ Soft Starter, S811+T..., S811+U..., and S811+V

### Multimedia

Soft Starter Product Family Overview

Soft starter DS7 up to 200 A

Soft Starter DS7 up to 32 A

### Specifications and datasheets

Eaton Specification Sheet - S811+V36N3S



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia