



# S8132

F28T5/835/ENV  
 28 watt; T5; Fluorescent; 3500K Neutral White; 85 CRI;  
 Miniature Bi Pin base

### Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8132

| Item Number   | UPC            | Watts          | Lamp Shape  | Base                | ANSI Base   | Lamp Code     | MOD In Inches |
|---------------|----------------|----------------|-------------|---------------------|-------------|---------------|---------------|
| S8132         | 045923081323   | 28             | T5          | Miniature Bi Pin    | G5          | F28T5/835/ENV | 0.63"         |
| MOL In Inches | Nominal Length | Initial Lumens | Mean Lumens | Average Rated Hours | Kelvin Temp | Color         | Pack          |
| 45.8"         | 48"            | 2900           | 2700        | 24000               | 3500        | Neutral White | 40            |
| Package Type  |                |                | CRI         | RoHS Compliant      |             |               |               |
| Sleeve        |                |                | 85          | Yes                 |             |               |               |



National Toll-Free:  
 800.43.SATCO  
 (800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
 New York, Florida, Texas,  
 Washington, California,  
 Puerto Rico

Corporate Offices:  
 110 Heartland Blvd.,  
 Brentwood, NY 11717  
 800.437.2826 631.243.2022  
 Fax 631.243.2027





# S8132

F28T5/835/ENV  
 28 watt; T5; Fluorescent; 3500K Neutral White; 85 CRI;  
 Miniature Bi Pin base

### Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8132

| Item Number   | UPC            | Watts          | Lamp Shape  | Base                | ANSI Base   | Lamp Code     | MOD In Inches |
|---------------|----------------|----------------|-------------|---------------------|-------------|---------------|---------------|
| S8132         | 045923081323   | 28             | T5          | Miniature Bi Pin    | G5          | F28T5/835/ENV | 0.63"         |
| MOL In Inches | Nominal Length | Initial Lumens | Mean Lumens | Average Rated Hours | Kelvin Temp | Color         | Pack          |
| 45.8"         | 48"            | 2900           | 2700        | 24000               | 3500        | Neutral White | 40            |
| Package Type  |                |                | CRI         | RoHS Compliant      |             |               |               |
| Sleeve        |                |                | 85          | Yes                 |             |               |               |



National Toll-Free:  
 800.43.SATCO  
 (800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
 New York, Florida, Texas,  
 Washington, California,  
 Puerto Rico

Corporate Offices:  
 110 Heartland Blvd.,  
 Brentwood, NY 11717  
 800.437.2826 631.243.2022  
 Fax 631.243.2027

