



S8133

F28T5/841/ENV
28 watt; T5; Fluorescent; 4100K Cool White; 85 CRI; Miniature Bi Pin base

Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8133

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | MOD In Inches |
|---------------|----------------|----------------|-------------|---------------------|-------------|---------------|---------------|
| S8133 | 045923081330 | 28 | T5 | Miniature Bi Pin | G5 | F28T5/841/ENV | 0.63" |
| MOL In Inches | Nominal Length | Initial Lumens | Mean Lumens | Average Rated Hours | Kelvin Temp | Color | Pack |
| 45.8" | 48" | 2900 | 2700 | 24000 | 4100 | Cool White | 40 |
| Package Type | CRI | RoHS Compliant | | | | | |
| Sleeve | 85 | Yes | | | | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S8133

F28T5/841/ENV
28 watt; T5; Fluorescent; 4100K Cool White; 85 CRI; Miniature Bi Pin base

Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8133

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | MOD In Inches |
|---------------|----------------|----------------|-------------|---------------------|-------------|---------------|---------------|
| S8133 | 045923081330 | 28 | T5 | Miniature Bi Pin | G5 | F28T5/841/ENV | 0.63" |
| MOL In Inches | Nominal Length | Initial Lumens | Mean Lumens | Average Rated Hours | Kelvin Temp | Color | Pack |
| 45.8" | 48" | 2900 | 2700 | 24000 | 4100 | Cool White | 40 |
| Package Type | CRI | RoHS Compliant | | | | | |
| Sleeve | 85 | Yes | | | | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

