



S8145

F54T5/841/HO/ENV
54 watt; T5; Fluorescent; 4100K Cool White; 85 CRI; Miniature Bi Pin base



Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards

S8145

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8145	045923081453	54	T5	Miniature Bi Pin	G5	F54T5/841/HO/ENV	0.63"
MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
45.8"	48"	5000	4650	24000	4100	Cool White	40
Package Type	CRI	RoHS Compliant					
Sleeve	85	Yes					



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S8145

F54T5/841/HO/ENV
54 watt; T5; Fluorescent; 4100K Cool White; 85 CRI; Miniature Bi Pin base



Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards

S8145

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8145	045923081453	54	T5	Miniature Bi Pin	G5	F54T5/841/HO/ENV	0.63"
MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
45.8"	48"	5000	4650	24000	4100	Cool White	40
Package Type	CRI	RoHS Compliant					
Sleeve	85	Yes					



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

