



# S8351

CFT32W/4P/835  
32 watt; pin-based Compact Fluorescent; 3500K; 82 CRI;  
GX24q-3 (4-Pin) base

### Features

- Non-integrated Pin Based CFL
- Uses 75% less energy than equivalent incandescent lamps
- TCLP compliant for low mercury
- Meets RoHS standards



S8351

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOL In Inches
S8351	045923083518	32	T4	GX24q-3	GX24q-3	CFT32W/4P/835	5.8"
Initial Lumens	Average Rated Hours	Kelvin Temp	Color	Pack	Package Type	CRI	RoHS Compliant
2400	15000	3500	Neutral White	50	Hang Box	82	Yes
UL Listed							
Yes							



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S8351

CFT32W/4P/835  
32 watt; pin-based Compact Fluorescent; 3500K; 82 CRI;  
GX24q-3 (4-Pin) base

### Features

- Non-integrated Pin Based CFL
- Uses 75% less energy than equivalent incandescent lamps
- TCLP compliant for low mercury
- Meets RoHS standards



S8351

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOL In Inches
S8351	045923083518	32	T4	GX24q-3	GX24q-3	CFT32W/4P/835	5.8"
Initial Lumens	Average Rated Hours	Kelvin Temp	Color	Pack	Package Type	CRI	RoHS Compliant
2400	15000	3500	Neutral White	50	Hang Box	82	Yes
UL Listed							
Yes							



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

