



S8356

CFT42W/4P/841
42 watt; pin-based Compact Fluorescent; 4100K; 82 CRI;
GX24q-4 (4-Pin) base

Features

- Non-integrated Pin Based CFL
- Uses 75% less energy than equivalent incandescent lamps
- TCLP compliant for low mercury
- Meets RoHS standards



S8356

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOL In Inches
S8356	045923083563	42	T4	GX24q-4	GX24q-4	CFT42W/4P/841	6.6"
Initial Lumens	Average Rated Hours	Kelvin Temp	Color	Pack	Package Type	CRI	RoHS Compliant
3200	15000	4100	Cool White	50	Hang Box	82	Yes
UL Listed							
Yes							



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S8356

CFT42W/4P/841
42 watt; pin-based Compact Fluorescent; 4100K; 82 CRI;
GX24q-4 (4-Pin) base

Features

- Non-integrated Pin Based CFL
- Uses 75% less energy than equivalent incandescent lamps
- TCLP compliant for low mercury
- Meets RoHS standards



S8356

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOL In Inches
S8356	045923083563	42	T4	GX24q-4	GX24q-4	CFT42W/4P/841	6.6"
Initial Lumens	Average Rated Hours	Kelvin Temp	Color	Pack	Package Type	CRI	RoHS Compliant
3200	15000	4100	Cool White	50	Hang Box	82	Yes
UL Listed							
Yes							



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

