



S8405

F17T8/835/ENV
17 watt; T8; Fluorescent; 3500K Neutral White; 85 CRI; Medium Bi Pin base



Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards

S8405

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8405	045923084058	17	T8	Medium Bi Pin	G13	F17T8/835/ENV	1.00"
MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
23.78"	24"	1450	1350	20000	3500	Neutral White	30
CRI	RoHS Compliant						
85	Yes						



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S8405

F17T8/835/ENV
17 watt; T8; Fluorescent; 3500K Neutral White; 85 CRI; Medium Bi Pin base



Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards

S8405

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8405	045923084058	17	T8	Medium Bi Pin	G13	F17T8/835/ENV	1.00"
MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
23.78"	24"	1450	1350	20000	3500	Neutral White	30
CRI	RoHS Compliant						
85	Yes						



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

