



# S8412

F25T8/841/ENV  
25 watt; T8; Fluorescent; 4100K Cool White; 85 CRI; Medium Bi Pin base



### Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards

S8412

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8412	045923084126	25	T8	Medium Bi Pin	G13	F25T8/841/ENV	1.00"
MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
35.78"	36"	2300	2185	20000	4100	Cool White	30
CRI	RoHS Compliant						
85	Yes						



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S8412

F25T8/841/ENV  
25 watt; T8; Fluorescent; 4100K Cool White; 85 CRI; Medium Bi Pin base



### Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards

S8412

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8412	045923084126	25	T8	Medium Bi Pin	G13	F25T8/841/ENV	1.00"
MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
35.78"	36"	2300	2185	20000	4100	Cool White	30
CRI	RoHS Compliant						
85	Yes						



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

