



# S8421

F32T8/850/ENV  
32 watt; T8; Fluorescent; 5000K Natural Light; 85 CRI; Medium Bi Pin base

### Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8421

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8421	045923084218	32	T8	Medium Bi Pin	G13	F32T8/850/ENV	1.00"
MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
47.78"	48"	2900	2750	24000	5000	Natural Light	30
CRI		RoHS Compliant					
85		Yes					



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S8421

F32T8/850/ENV  
32 watt; T8; Fluorescent; 5000K Natural Light; 85 CRI; Medium Bi Pin base

### Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8421

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8421	045923084218	32	T8	Medium Bi Pin	G13	F32T8/850/ENV	1.00"
MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
47.78"	48"	2900	2750	24000	5000	Natural Light	30
CRI		RoHS Compliant					
85		Yes					



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

